

Quality Water Analysis Equipment

pH / ORP CONDUCTIVITY DISSOLVED OXYGEN STANDARDS

## **MODEL 403 BALL VALVE CONDUCTIVITY SENSOR Specification**

| Specifications                                      | Model<br>403-0.01   | Model<br>403-0.02   | Model<br>403-0.1  | Model<br>403-0.2  | Model<br>403-1.0  | Model<br>403-2.0  | Model<br>403-5.0  |
|---|---|---|---|---|---|---|---|
| Measurement<br>Range                                | 0 μS/cm to 10 μS/cm   | 0 μS/cm to 20 μS/cm   | 10 μS/cm to<br>1 000 μS/cm  | 20 μS/cm to<br>2 000 μS/cm  | 10 μS/cm to<br>10 000 μS/cm   | 20 μS/cm to<br>20 000 μS/cm   | 50 μS/cm to<br>50 000 μS/cm   |
| Temperature<br>Range                                | 0 °C to 150 °C<br>(32 °F to 302 °F)   | 0 °C to 150 °C<br>(32 °F to 302 °F)   | 0 °C to 150 °C<br>(32 °F to 302 °F)   | 0 °C to 150 °C<br>(32 °F to 302 °F)   | 0 °C to 150 °C<br>(32 °F to 302 °F)   | 0 °C to 150 °C<br>(32 °F to 302 °F)   | 0 °C to 150 °C<br>(32 °F to 302 °F)   |
| Pressure Range                                      | 0 kPa to 689 kPa<br>(0 psi to 100 psi)  | 0 kPa to 689 kPa<br>(0 psi to 100 psi)  | 0 kPa to 689 kPa<br>(0 psi to 100 psi)  | 0 kPa to 689 kPa<br>(0 psi to 100 psi)  | 0 kPa to 689 kPa<br>(0 psi to 100 psi)  | 0 kPa to 689 kPa<br>(0 psi to 100 psi)  | 0 kPa to 689 kPa<br>(0 psi to 100 psi)  |
| Sensing Element                                     | Stainless Steel   | Stainless Steel   | Stainless Steel   | Stainless Steel   | Titanium  | Titanium  | Titanium  |
| Wetted Materials                                    | Stainless Steel,<br>PEEK, Viton   | Stainless Steel,<br>PEEK, Viton   | Stainless Steel,<br>PEEK, Viton   | Stainless Steel,<br>PEEK, Viton   | Stainless Steel,<br>PEEK, Titanium,<br>Viton  | Stainless Steel,<br>PEEK, Titanium,<br>Viton  | Stainless Steel,<br>PEEK, Titanium,<br>Viton  |
| Temperature<br>Sensor                               | 1000 Ω PT RTD   |
| Process<br>Connections                              | 0.75 in MNPT for<br>direct insertion;<br>1.0 in MNPT<br>via ball valve                    | 0.75 in MNPT for<br>direct insertion;<br>1.0 in MNPT<br>via ball valve                    | 0.75 in MNPT for<br>direct insertion;<br>1.0 in MNPT<br>via ball valve                    | 0.75 in MNPT for<br>direct insertion;<br>1.0 in MNPT<br>via ball valve                    | 0.75 in MNPT for<br>direct insertion;<br>1.0 in MNPT<br>via ball valve                    | 0.75 in MNPT for<br>direct insertion;<br>1.0 in MNPT<br>via ball valve                    | 0.75 in MNPT for<br>direct insertion;<br>1.0 in MNPT<br>via ball valve                    |
| Pressure &<br>Temperature<br>Limits at<br>Insertion | 689 kPa at 100 °C<br>(100 psi at 212 °F)<br>to<br>517 kPa at 150 °C<br>(75 psi at 302 °F) | 689 kPa at 100 °C<br>(100 psi at 212 °F)<br>to<br>517 kPa at 150 °C<br>(75 psi at 302 °F) | 689 kPa at 100 °C<br>(100 psi at 212 °F)<br>to<br>517 kPa at 150 °C<br>(75 psi at 302 °F) | 689 kPa at 100 °C<br>(100 psi at 212 °F)<br>to<br>517 kPa at 150 °C<br>(75 psi at 302 °F) | 689 kPa at 100 °C<br>(100 psi at 212 °F)<br>to<br>517 kPa at 150 °C<br>(75 psi at 302 °F) | 689 kPa at 100 °C<br>(100 psi at 212 °F)<br>to<br>517 kPa at 150 °C<br>(75 psi at 302 °F) | 689 kPa at 100 °C<br>(100 psi at 212 °F)<br>to<br>517 kPa at 150 °C<br>(75 psi at 302 °F) |
| Electrode<br>Dimensions                             | Length:<br>41.9 cm (16.5 in)<br>Diameter:<br>1.91 cm (0.75 in)                            |
| Ball Valve (BV)<br>Electrode<br>Dimensions          | Retracted BV length:<br>68.8 cm (27.0 in)<br>Inserted BV length:<br>55.9 cm (22.0 in)     | Retracted BV length:<br>68.8 cm (27.0 in)<br>Inserted BV length:<br>55.9 cm (22.0 in)     | Retracted BV length:<br>68.8 cm (27.0 in)<br>Inserted BV length:<br>55.9 cm (22.0 in)     | Retracted BV length:<br>68.8 cm (27.0 in)<br>Inserted BV length:<br>55.9 cm (22.0 in)     | Retracted BV length:<br>68.8 cm (27.0 in)<br>Inserted BV length:<br>55.9 cm (22.0 in)     | Retracted BV length:<br>68.8 cm (27.0 in)<br>Inserted BV length:<br>55.9 cm (22.0 in)     | Retracted BV length:<br>68.8 cm (27.0 in)<br>Inserted BV length:<br>55.9 cm (22.0 in)     |
| Maximum<br>Electrode<br>Insertion Depth             | 22.9 cm (9.0 in)  |
| Weight  | 2.3 kg (5.0 lb)   |
| Shipping Weight                                     | 3.2 kg (7.0 lb)   |
| Shipping<br>Dimensions                              | 81 cm × 15 cm × 15 cm<br>(32 in × 6 in × 6 in)  | 81 cm × 15 cm × 15 cm<br>(32 in × 6 in × 6 in)  | 81 cm × 15 cm × 15 cm<br>(32 in × 6 in × 6 in)  | 81 cm × 15 cm × 15 cm<br>(32 in × 6 in × 6 in)  | 81 cm × 15 cm × 15 cm<br>(32 in × 6 in × 6 in)  | 81 cm × 15 cm × 15 cm<br>(32 in × 6 in × 6 in)  | 81 cm × 15 cm × 15 cm<br>(32 in × 6 in × 6 in)  |

29 Centennial Road, Orangeville, ON, L9W 1R1 Phone: (519) 941-8161 Fax: (519) 941-8164 Toll Free (North America) 1-800-265-9161 Internet: sales@iccontrols.com